



quick ENTSCÄUMER

Prevents the foam building

Area of application

Destroys foam or prevents foaming. Suitable for all types of cleaning equipment



Application

Pour product undiluted into the suction hose or load the recovery tank with 10 – 50 ml QUICK ENTSCÄUMER per litre tank volume, depending on the degree of foaming. The dosage corresponds to a 1 – 5% concentration in the tank.

Product characteristics

- Prevents foaming in cleaning equipment
- Immediately dissolves foam as it forms
- Simple application (e.g. directly into recovery tank)

Technical information

Carton of 6 x 500 bottles
10 litre canister

order No. 00194
order No. 30862

All information contained in our brochures is accurate to the best of our knowledge and experience. No liability can be derived from the information herein. For details about the product, please refer to the safety data sheet. (GB) 0218

pH conc

0	2	4	6	10	12	14
---	---	---	---	----	----	----

DR.SCHNELL GmbH & Co. KGaA
Taunusstraße 19 · 80807 Munich
Tel. +49 89 3506080
info@dr-schnell.com
www.dr-schnell.com

Wir leben Hygiene
DR.SCHNELL
QUALITÄT UND SERVICE